

Displacement encoder MME-MTS-360-TLF-AIF

Part number: 178308

FESTO



Data sheet

| Feature | Value |
|--|---|
| CE mark (see declaration of conformity) | To EU EMC Directive In accordance with EU RoHS Directive |
| CE marking (see declaration of conformity) | To UK instructions for EMC To UK RoHS instructions |
| Functional principle of measuring system | Digital |
| Ambient temperature | -40 °C...75 °C |
| Max. travel speed | 10 m/s |
| Max. travel acceleration | 200 m/s ² |
| Displacement resolution | 0.01 mm |
| Non-dependent linearity | 0.02% Min. ± 50 µm |
| Temperature coefficient | 15 ppm/K |
| Stroke | 360 mm |
| Output signal | CAN protocol type SPC-AIF |
| Nominal operating voltage DC | 24 V |
| Permissible voltage fluctuations | -15%/+20% |
| Max. current consumption | 90 mA |
| Electrical connection | 6-pin Plugs To DIN 45322 Round design |
| Design | Closed profile With moving slide |
| Parallel offset of coupling | ± 1.5 mm |
| Angle offset of driver | ± 1 ° |
| Mounting position | optional |
| Product weight | 780 g |
| Material housing | Wrought aluminium alloy Anodised |
| Material slide housing | PBT-reinforced Permanent magnet |
| Material slide coupling | Steel |
| Material cover | Die-cast aluminium Painted |

| Feature | Value |
|---|--------------------------------------|
| Material mounting clips | PEI |
| Degree of protection | IP65 To IEC 60529 |
| Vibration resistance to DIN/IEC 68 Part 2-6 | Tested according to severity level 1 |
| Continuous shock resistance to DIN/IEC 68 Part 2-82 | Tested according to severity level 1 |
| LABS (PWIS) conformity | VDMA24364-B2-L |