



## LFR-M1-G1/4-E10UGK

### Filter regulator

Feature	Data/description
Size	1
Series	M
Actuator lock	Rotary knob with lock
Grade of filtration	40 µm
Condensate drain	fully automatic
Design structure	Filter regulator with pressure gauge
Max. condensate volume	10,25 cm <sup>3</sup>
Bowl guard	Plastic guard
Pressure gauge	with pressure gauge
Pressure control range	0 - 10 bar
Inlet pressure 1	0 - 17 bar
Max. pressure hysteresis	0,4 bar
Standard nominal flow rate	2.000 l/min
Operating medium	Compressed air
Medium temperature	-10 - 80 °C
Ambient temperature	-10 - 80 °C
Product weight	374 g
Mounting type	Optional Line installation with accessories
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Materials note	Contains PWIS substances
Materials information, housing	Zinc die-casting



Data sheet

Part no.: **179358**

Page:2

## **LFR-M1-G1/4-E10UGK**

### **Filter regulator**

<b>Feature</b>	<b>Data/description</b>
Materials information for bowl	Zinc die-casting