

ISO cylinder DSBC-125-500-PPSA-N3

Part number: 1804673

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 500 mm |
| Piston diameter | 125 mm |
| Piston rod thread | M27x2 |
| Cushioning | Self-adjusting pneumatic end-position cushioning |
| Mounting position | optional |
| Conforms to standard | ISO 15552 |
| Piston-rod end | Male thread |
| Design | Piston Piston rod Profile barrel |
| Position detection | Via proximity switch |
| Variants | Piston rod at one end |
| Operating pressure | 0.02 MPa...1 MPa 0.2 bar...10 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C...80 °C |
| Impact energy in end positions | 3.3 J |
| Cushioning length | 45 mm |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke | 6881 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 7363 N |
| Moving mass for 0 mm stroke | 2245 g |
| Additional moving mass per 10 mm stroke | 63 g |
| Basic weight for 0 mm stroke | 6611 g |
| Additional weight per 10 mm stroke | 151 g |
| Type of mounting | Either: Via female thread With accessories |
| Pneumatic connection | G1/2 |

| Feature | Value |
|----------------------------|---|
| Note on materials | RoHS-compliant |
| Material cover | Die-cast aluminium, coated |
| Material piston seal | TPE-U(PU) |
| Material piston | Wrought aluminium alloy |
| Material piston rod | High-alloy steel |
| Material piston rod wiper | TPE-U(PU) |
| Buffer seal material | TPE-U(PU) |
| Cushioning piston material | POM |
| Material cylinder barrel | Smooth-anodised wrought aluminium alloy |
| Material nut | Galvanised steel |
| Material bearing | POM |
| Material collar screws | Galvanised steel |