

# Push-in Y-fitting QSY-M5-6

Part number: 190674

FESTO



## Data sheet

Feature	Value
Size	Standard
Nominal size	2.4 mm
Type of seal on screwed plug	Sealing ring
Mounting position	optional
Design	Y-shape Push-pull principle
Size of pack	10
Operating pressure complete temperature range	-0.095 MPa...0.6 MPa -0.95 bar...6 bar -13.775 psi...87 psi
Temperature-dependent operating pressure	-0.095 MPa...1.4 MPa -0.95 bar...14 bar -13.775 psi...203 psi
Maritime classification	See certificate
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration at <a href="http://www.festo.com">www.festo.com</a>
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom class	Class 4 according to ISO 14644-1
Ambient temperature	-10 °C...80 °C
Nominal torque	1.33 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	13 g
Number of outputs	2
Number of supply lines	1
Type of mounting	External hexagon, size 10 mm
Pneumatic connection, port 1	Male thread M5
Pneumatic connection, port 2	For tubing outside diameter of 6 mm
Colour of release ring	Blue
Note on materials	RoHS-compliant
Material housing	PBT
Material release ring	POM

Feature	Value
Material tubing seal	NBR
Material tubing clamp component	High-alloy stainless steel