

# Tandem cylinder DNCT-3<sup>\*\*\*</sup> - -PPV-A

Part number: 191228

FESTO



## Data sheet

Feature	Value
Stroke	3 mm...500 mm
Based on standard	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Cushioning	Pneumatic cushioning, adjustable at both ends
Mode of operation	Double-acting
Operating pressure	0.06 MPa...1 MPa 0.6 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Cushioning length	32 mm
Pneumatic connection	3/8 NPT
Note on materials	RoHS-compliant
Material cover	Die-cast aluminium
Material seals	NBR TPE-U(PU)
Material housing	Wrought aluminium alloy
Material piston rod	High-alloy steel