

Solenoid valve



MN2H-2X3G-D-02-S-ZSR

Part number: 191371

FESTO

with central plug, round

Products to be discontinued. Available until 2009.



Data sheet

Feature	Value
Valve function	2x3/2 closed, single solenoid
Type of actuation	electrical
Width	18 mm
Standard nominal flow rate	440 l/min
Operating pressure	2 ... 10 bar
Design structure	Piston slide
Type of reset	Air spring
Protection class	IP65
Nominal size	6 mm
Grid dimension	19 mm
Exhaust-air function	throttleable
Sealing principle	soft
Assembly position	Any
Conforms to standard	VDMA 24563
Manual override	with accessories, detenting
Type of piloting	Piloted
Pilot air supply	external
Flow direction	non reversible
Pilot pressure	1.3 ... 10 bar
b value	0.3
C value	1.85 l/sbar
Switching time off	15 ms
Switching time on	15 ms
Characteristic coil data	24V DC: 1,5W
Operating medium	filtered compressed air, grade of filtration 40 µm, lubricated or unlubricated Vacuum
Corrosion resistance classification CRC	2
Medium temperature	-10 ... 50 °C
Pilot medium	filtered compressed air, grade of filtration 40 µm, lubricated or unlubricated
Ambient temperature	-10 ... 50 °C
Product weight	210 g
Electrical connection	Central plug Round design M12x1
Mounting type	with through hole
Auxiliary pilot air port 12/14	Sub-base VDMA 24563 size 2
Pilot exhaust port 82/84	Sub-base VDMA 24563 size 2
Pneumatic connection, port 1	Sub-base VDMA 24563 size 2
Pneumatic connection, port 2	Sub-base VDMA 24563 size 2
Pneumatic connection, port 3	Sub-base VDMA 24563 size 2
Pneumatic connection, port 4	Sub-base VDMA 24563 size 2
Pneumatic connection, port 5	Sub-base VDMA 24563 size 2
Materials information for seals	NBR
Materials information, housing	Aluminium die cast