

Push-in T-fitting QSTF-G3/8-10

Part number: 186206

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal size	8 mm
Type of seal on screwed plug	Sealing ring
Mounting position	optional
Design	L-shape, additional connection, female thread, lengthwise Push-pull principle
Size of pack	1
Operating pressure complete temperature range	-0.095 MPa...0.6 MPa -0.95 bar...6 bar -13.775 psi...87 psi
Temperature-dependent operating pressure	-0.095 MPa...1.4 MPa -0.95 bar...14 bar -13.775 psi...203 psi
Maritime classification	See certificate
Operating medium	Compressed air to ISO 8573-1:2010 [7:--] Water as per manufacturer's declaration at www.festo.com
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom class	Class 4 according to ISO 14644-1
Ambient temperature	-10 °C...80 °C
Nominal torque	15.5 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	74 g
Number of outputs	2
Number of supply lines	1
Type of mounting	External hexagon, size 24 mm
Pneumatic connection, port 1	Male thread G3/8
Pneumatic connection, port 2	Female thread G3/8 For tubing outside diameter of 10 mm
Colour of release ring	Blue
Note on materials	RoHS-compliant
Material housing	PBT

Feature	Value
Material hollow bolt	Nickel-plated brass
Material release ring	POM
Material tubing seal	NBR
Material tubing clamp component	High-alloy stainless steel