

# Fine filter LFMB-1/2-D-MAXI-A

Part number: 186474

FESTO



## Data sheet

Feature	Value
Series	D
Size	Maxi
Design	Fibre filter
Grade of filtration	1 µm
Condensate drain	Fully automatic
Operating pressure	2 bar...12 bar
Operating medium	Compressed air to ISO 8573-1:2010 [6:8:4] Inert gases
Air purity class at output	Compressed air to ISO 8573-1:2010 [5:7:3] Inert gases
Max. standard flow rate for clean air class	2400 l/min
Min. standard flow rate for clean air class	800 l/min
Filter efficiency	99.99 %
Max. condensate volume	80 cm <sup>3</sup>
Bowl guard	Metal bowl guard
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	1.5 °C...60 °C
Ambient temperature	-10 °C...60 °C
Storage temperature	-10 °C...60 °C
Residual oil content	0.5 mg/m <sup>3</sup>
Type of mounting	Either: In-line installation With accessories
Mounting position	Vertical +/-5°
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/2
Material housing	Die-cast zinc
Material filter	Borosilicate fibre
Material bowl	PC
Note on materials	RoHS-compliant
Product weight	1200 g