



flat cylinder DZF-1/2"-3"-A-P-A

Part number: 194117

FESTO

Non-rotating, for position sensing, with elastic cushioning rings in end positions. Various mounting options, with or without additional mounting components.



Data sheet

| Feature | Value |
|--|---|
| Stroke | 3 " |
| Piston diameter | 1/2" |
| Max. angular deflection of piston rod +/- | 2.5 deg |
| Cushioning | P: Flexible cushioning rings/plates at both ends |
| Mode of operation | double-acting |
| Protection against torque/guide | Oval piston |
| Operating pressure MPa | 0.16 ... 1 MPa |
| Operating pressure | 1.6 ... 10 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 ... 80 °C |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 51 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance | 68 N |
| Moving mass with 0 mm stroke | 12 g |
| Additional weight per 10 mm stroke | 2 g |
| Basic weight for 0 mm stroke | 96 g |
| Pneumatic connection | 10-32 UNF-2B |
| Material cover | Aluminium |
| Material seals | FPM TPE-U(PU) |
| Material housing | Wrought Aluminium alloy |
| Material piston rod | High alloy steel, non-corrosive |