



## MAS-10-N--AA-MOFK

### Fluidic muscle

Feature	Data/description
Size	10
Hysteresis	< 4% of the length of the tubing
Max. contraction	25% of tubing length
Max. initial tension	3% of tubing length
Relaxation at room temperature	< 4% of the length of the tubing
Tubing length	40 - 9.000 mm
Repetition accuracy	< 1 %
Assembly position	Any
Operating pressure	0 - 8 bar
Mode of operation	single-acting pulling action
Operating medium	Lubricated compressed air Compressed air, filtered, unlubricated
Corrosion resistance classification CRC	2
Theoretical force at 6 bar	400 N
Additional weight per 1 m length	94 g
Product weight for 0 m length	81 g
Pneumatic connection	M10x1,25
Materials information for locknut	Wrought Aluminium alloy neutral anodisation
Materials note	Contains PWIS substances Copper and PTFE-free
Materials information for flange	Wrought Aluminium alloy blue anodised
Materials information for sleeve	Steel Galvanised

**MAS-10-N--AA-MOFK****Fluidic muscle**

Feature	Data/description
Materials information for membrane	CR AR