


Parallel gripper HGPP-20-A

Part number: 187873

FESTO



Data sheet

Feature	Value
Size	20
Stroke per gripper jaws	7.5 mm
Max. replacement accuracy	0.1 mm
Repetition accuracy, gripper	0.02 mm
Number of gripper jaws	2
Drive system	Pneumatic
Mode of operation	Double-acting
Gripper function	Parallel
Gripper force back-up	None
Design	Rack and pinion
Position detection	Via Hall sensor Via inductive sensors
Total gripping force, opening, 0.6MPa (6bar, 87 psi)	340 N
Total gripping force, closing, 0.6MPa (6bar, 87 psi)	340 N
Operating pressure	2 bar...8 bar
Max. operating frequency of gripper	4 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	44 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	59 ms
Max. mass per external gripper finger	200 g
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	5 °C...60 °C
Gripper force per gripper jaw, opening, 0.6 MPa (6 bar, 87 psi)	170 N
Gripper force per gripper jaw, closing, 0.6 MPa (6 bar, 87 psi)	170 N
Max. force on gripper jaw Fz static	220 N
Max. torque at gripper Mx static	14 Nm
Max. torque at gripper My static	14 Nm
Max. torque at gripper Mz static	14 Nm
Product weight	604 g

Feature	Value
Type of mounting	Via female thread
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover cap	POM
Material housing	Hard anodised wrought aluminium alloy
Material gripper jaws	Wrought aluminium alloy, nickel-plated