


Short-stroke cylinder AEVC-6-10-P

Part number: 188059

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 10 mm |
| Piston diameter | 6 mm |
| Spring return force with retracted piston rod | 3 N |
| Cushioning | Elastic cushioning rings/plates at both ends |
| Mounting position | optional |
| Mode of operation | Single-acting Pushing |
| Design | Piston Piston rod |
| Position detection | Without |
| Operating pressure | 0.25 MPa...0.8 MPa 2.5 bar...8 bar 36.25 psi...116 psi |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C...80 °C |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 11 N |
| Moving mass | 1.4 g |
| Product weight | 11 g |
| Type of mounting | Either: With through-hole With accessories |
| Pneumatic connection | M3 |
| Note on materials | RoHS-compliant |
| Material cover | Wrought aluminium alloy Anodised |
| Material seals | NBR TPE-U(PU) |
| Material housing | Wrought aluminium alloy Anodised |
| Material piston rod | High-alloy steel |