

# Short-stroke cylinder AEVC-20-25-I-P

Part number: 188133

FESTO



## Data sheet

| Feature                                                      | Value                                                                                      |
|--------------------------------------------------------------|--------------------------------------------------------------------------------------------|
| Stroke                                                       | 25 mm                                                                                      |
| Piston diameter                                              | 20 mm                                                                                      |
| Spring return force with retracted piston rod                | 10 N                                                                                       |
| Cushioning                                                   | Elastic cushioning rings/plates at both ends                                               |
| Mounting position                                            | optional                                                                                   |
| Mode of operation                                            | Single-acting<br>Pushing                                                                   |
| Design                                                       | Piston<br>Piston rod                                                                       |
| Position detection                                           | Without                                                                                    |
| Operating pressure                                           | 0.15 MPa...1 MPa<br>1.5 bar...10 bar<br>21.75 psi...145 psi                                |
| Operating medium                                             | Compressed air to ISO 8573-1:2010 [7:4:4]                                                  |
| Note on operating and pilot medium                           | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                               | 1 - Low corrosion stress                                                                   |
| LABS (PWIS) conformity                                       | VDMA24364-B1/B2-L                                                                          |
| Ambient temperature                                          | -20 °C...80 °C                                                                             |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 170 N                                                                                      |
| Moving mass                                                  | 32 g                                                                                       |
| Product weight                                               | 127 g                                                                                      |
| Type of mounting                                             | Either:<br>With through-hole<br>With accessories                                           |
| Pneumatic connection                                         | M5                                                                                         |
| Note on materials                                            | RoHS-compliant                                                                             |
| Material cover                                               | Wrought aluminium alloy<br>Anodised                                                        |
| Material seals                                               | NBR<br>TPE-U(PU)                                                                           |
| Material housing                                             | Wrought aluminium alloy<br>Anodised                                                        |
| Material piston rod                                          | High-alloy steel                                                                           |