

# round cylinder DSNU-63-250-PPV-A

Part number: 196058

FESTO

For position sensing, with adjustable end-position cushioning. Various mounting options, with or without additional mounting components.



## Data sheet

Feature	Value
Stroke	250 mm
Piston diameter	63 mm
Piston rod thread	M16x1,5
Cushioning	PPV: Pneumatic cushioning adjustable at both ends
Assembly position	Any
Design structure	Piston Piston rod Cylinder barrel
Position detection	For proximity sensor
Operating pressure MPa	0.1 ... 1 MPa
Operating pressure	1 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 ... 80 °C
Cushioning length	21 mm
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	1,681.9 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	1,870.3 N
Moving mass	1,084 g
Product weight	2,545 g
Mounting type	with accessories
Pneumatic connection	G3/8
Materials note	Conforms to RoHS
Material cover	Wrought Aluminium alloy
Material seals	NBR TPE-U(PU)
Material piston rod	High alloy steel
Material cylinder barrel	High alloy steel, non-corrosive