


# Axial kit EAMM-A-N48-60G

Part number: 1972527

FESTO



## Data sheet

Feature	Value
Mounting position	optional
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Transmittable torque	12.5 Nm
Product weight	509 g
Interface code, actuator	N48
Interface code, motor in	60G
Note on materials	RoHS-compliant