

QST-CM-M5-6**Push-in T-fitting**

| Feature | Data/description |
|---|--|
| Design structure | Push/pull principle |
| Ambient temperature | 0 - 40 °C |
| Pneumatic connection | Male thread M5 for tubing, 6mm outside diameter |
| Operating pressure | -0,950 - 6,000 bar |
| Medium temperature | 0,0 - 40,0 °C |
| Operating medium | Filtered compressed air Vacuum |
| Nominal size | 1,800 mm |
| Size | Standard |
| Corrosion resistance classification CRC | 1 |
| Type of seal on screw-in stud | Sealing ring |
| Surface resistance | 0,010 - 10,000 MOhm |
| Materials note | Antistatic |
| Max. tightening torque | 1,500 Nm |
| Materials information, housing | PBT-reinforced |