

Axial kit EAMM-A-P10-38A-40G

Part number: 2297648

FESTO



Data sheet

Feature	Value
Mounting position	optional
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Transmittable torque	12.5 Nm
Product weight	190 g
Interface code, actuator	P10-38A
Interface code, motor in	40G
Interface code, clutch housing	38A
Note on materials	RoHS-compliant