

ISO cylinder DSBG-200-400-PPVA-N3

Part number: 2390149

FESTO



Data sheet

Feature	Value
Stroke	400 mm
Piston diameter	200 mm
Piston rod thread	M36x2
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	optional
Conforms to standard	ISO 15552
Piston-rod end	Male thread
Design	Piston Piston rod Tie rod Cylinder barrel
Position detection	Via proximity switch
Variants	Piston rod at one end
Operating pressure	0.06 MPa...1 MPa 0.6 bar...10 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...80 °C
Impact energy in end positions	4.8 J
Cushioning length	48 mm
Cushioning length, advance stroke	48 mm
Cushioning length, return stroke	48 mm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	18096 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	18850 N
Moving mass	9228 g
Moving mass for 0 mm stroke	5348 g
Additional moving mass per 10 mm stroke	97 g
Product weight	25333 g
Basic weight for 0 mm stroke	15493 g

Feature	Value
Additional weight per 10 mm stroke	246 g
Type of mounting	Either: Via female thread With accessories
Pneumatic connection	G3/4
Note on materials	RoHS-compliant
Material cover	Cast aluminium, coated
Material piston seal	NBR
Material piston	Cast aluminium
Material piston rod	High-alloy steel
Material piston rod wiper	NBR
Buffer seal material	TPE-U(PU)
Cushioning piston material	POM
Material cylinder barrel	Smooth-anodised wrought aluminium alloy
Material nut	Galvanised steel
Material bearing	Metal polymer compound
Material collar nut	Galvanised steel
Material tie rod	High-alloy steel