

ISO cylinder DNC-50-30-PPV-A

Part number: 1922630

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 30 mm |
| Piston diameter | 50 mm |
| Piston rod thread | M16x1.5 |
| Cushioning | Pneumatic cushioning, adjustable at both ends |
| Mounting position | optional |
| Conforms to standard | ISO 15552 |
| Piston-rod end | Male thread |
| Design | Piston Piston rod Profile barrel |
| Position detection | Via proximity switch |
| Variants | Piston rod at one end |
| Operating pressure | 0.06 MPa...1.2 MPa 0.6 bar...12 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C...80 °C |
| Impact energy in end positions | 0.2 J |
| Cushioning length | 22 mm |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke | 990 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 1178 N |
| Moving mass for 0 mm stroke | 538 g |
| Additional moving mass per 10 mm stroke | 25 g |
| Basic weight for 0 mm stroke | 1260 g |
| Additional weight per 10 mm stroke | 64 g |
| Type of mounting | Via female thread With accessories |
| Pneumatic connection | G1/4 |
| Note on materials | RoHS-compliant |

| Feature | Value |
|--------------------------|--|
| Material cover | Die-cast aluminium Coated |
| Material seals | TPE-U(PU) |
| Material piston rod | High-alloy steel |
| Material cylinder barrel | Wrought aluminium alloy Smooth anodised |