

## CPE10SC-M1BH-3GL-QS-4-P

Solenoid valve

Data sheet

Part no.: 192517

Page:1

Feature	Data/description
Switching function	<b>3/2-way valve, normally closed</b>
Switching function short code	<b>3/2</b>
Direction of flow reversible	<b>No</b>
Operating principle	<b>Slide</b>
Shape of function component	<b>Piston</b>
With exhaust flow control	<b>Yes</b>
Type of regulation	<b>Indirect</b>
Control type	<b>Monostable</b>
Type of reset	<b>Air spring</b>
Type of mounting	<b>Screw</b>
Installation position	<b>Any</b>
Nominal size	<b>3 mm</b>
Operating pressure min.	<b>3 bar</b>
Operating pressure max.	<b>8 bar</b>
Minimum ambient temperature	<b>-5 °C</b>
Maximum ambient temperature	<b>50 °C</b>
Minimum medium temperature	<b>-5 °C</b>
Maximum medium temperature	<b>50 °C</b>
Type of connection, air supply	<b>Sub-base</b>
Air connection type power port	<b>Push-in</b>
Nominal size of tubing connection, worki	<b>4</b>
Type of connection, exhaust	<b>Sub-base</b>
Air connection type aux. pilot air suppl	<b>Internal</b>
Air connection type aux. pilot air exhau	<b>Thread</b>
Connecting thread for aux. pilot air exh	<b>M 3</b>
Type pilot control air Supply and exhaus	<b>External pilot air and air spring, ducted pilot ex</b>
Actuation/reset	<b>Single solenoid, air spring return</b>
Manual override	<b>Non-detenting (detenting with attachment)</b>
Operating status display	<b>No</b>
Material of cap	<b>PA-reinforced</b>
Material of housing	<b>AL, die-cast metal</b>

**CPE10SC-M1BH-3GL-QS-4-P**

Solenoid valve

Data sheet

Part no.: 192517

Page:2

<b>Feature</b>	<b>Data/description</b>
Material of seals	<b>NBR-Elastomer</b>
CT criterion	<b>Free of copper and PTFE</b>
Product weight	<b>0,05 kg</b>
Standard nominal flow rate 1 - 2	<b>200 l/min</b>
Standard nominal flow rate 2 - 3	<b>200 l/min</b>
Response time OFF/OVER (dom.)	<b>11 ms</b>
Response time OFF/OVER	<b>15 ms</b>
Voltage type	<b>DC</b>
Nominal voltage	<b>24 V</b>
Medium	<b>Filtered compr. air (40 µm) (may be lubricated)</b>
Degree of protection	<b>IP65</b>