

# Feed separator HPVS-14-20-A

Part number: 2095360

FESTO



## Data sheet

Feature	Value
Stroke	20 mm
Piston diameter	14 mm
Max. replacement accuracy	0.3 mm
Max. stem backlash Sx	0.05 mm
Max. stem backlash Sz	0.03 mm
Max. angular gripper jaw backlash ax	0.12 deg
Max. angular gripper jaw backlash ay	0.2 deg
Max. angular gripper jaw backlash az	0.175 deg
Mounting of external fingers	Through-hole
Cushioning	No cushioning
Mounting position	optional
Mode of operation	Double-acting
Design	Piston rod Non-rotating
Position detection	Via proximity switch
Protection against torque/guide	Square guide
Operating pressure	3 bar...8 bar
Advance time	50 ms
Return-stroke time	138 ms
Repetition accuracy	0.15 mm
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	5 °C...60 °C
Max. force on finger Fz static	100 N
Max. torque Mr at finger, static	5 Nm
Max. torque at finger Mx static	5 Nm
Max. torque at finger My static	5 Nm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	75 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	90 N

<b>Feature</b>	<b>Value</b>
Product weight	183 g
Max. mass per external gripper finger	150 g
alternative connections	M5
Type of mounting	Either: Via female thread and centring sleeve Via through-hole and centring sleeve
Pneumatic connection	M5
Note on materials	RoHS-compliant