


# Motor controller

## CMMP-AS-C10-11A-P3-M0-C1

Part number: 2385043

FESTO

This product is only available if ordered from the Festo Corporation, USA.



## Data sheet

Feature	Value
Mains filter	Integrated
Safety function	Safe stop 1 (SS1) Safe torque off (STO)
Safety Integrity Level (SIL)	STO / SIL 3 / SILCL 3
Performance level (PL)	Safe Torque off (STO)/Category 4, Performance Level e
Display	Seven-segment display
Output frequency	0 ... 1,000 Hz
Output voltage range AC	3x 0 - 360 V
Braking resistance	68 Ohm
Diagnostic coverage	97.07 %
Digital logic output characteristics	Electrically isolated Freely configurable to a given extent
Hardware fault tolerance	1
Setpoint input impedance	20 kOhm
Braking resistance pulse power	8.5 kVA
Max. current, digital logic outputs	100 mA
Max. peak current duration	5 s
Max. intermediate circuit voltage, DC	560 V
Nominal output current	10 A
Nominal operating voltage, AC	400 V
Nominal controller power	6,000 VA
Nominal DC voltage, logic power supply	24 V
Nominal current	11 A
Effective nominal current per phase	10 A
Line frequency	50 ... 60 Hz
Parameters configuring interface	Ethernet USB Parameters configuration and commissioning
Nominal operating voltage, phases	Three-phase
SFF Safe Failure Fraction	99.17 %
Peak power	12,000 VA
Effective peak current per phase	20 A
Current consumption, logic power supply without clamping brake	1 A
Degree of contamination	2
Permissible range, logic voltage	± 20 %
Permissible voltage fluctuation	+/- 10 %
Certificate issuing department	TÜV Rheinland
CE mark (see declaration of conformity)	to EU directive low-voltage devices to EU directive for machinery to EU directive for EMC
Storage temperature	-25 ... 70 °C
Relative air humidity	0 - 90 %
Protection class	IP20
Ambient temperature	0 ... 40 °C

<b>Feature</b>	<b>Value</b>
Authorisation	RCM Mark c UL us - Listed (OL)
Proof test interval	20 a
Product weight	3,800 g
Number of analogue monitor outputs	2
Number of analogue setpoint inputs	2
Number of 24 V DC digital logic outputs	5
Number of digital logic inputs	10
Communications profile	DS301/DSP402
Process interface	I/O coupling For 256 position sets
Logic input working range	8 ... 30 V
Monitor output working range	± 10 V
Setpoint input working range	± 10 V
Monitor output resolution	9 Bit
Encoder interface output, characteristics	Resolution 16384 ppr
Encoder interface input, characteristics	SINCOS EnDat HIPERFACE RS422 3-phase encoding signals
Monitor output characteristics	Short-circuit proof
Setpoint input characteristics	Differential inputs Can be configured for current Can be configured for speed in RPM
Logic input characteristics	Freely configurable Electrically isolated
Encoder interface output, function	Actual value feedback via encoder signals in speed control mode Setpoint specification for downstream slave drive unit
Encoder interface input, function	Encoder signal, speed setpoint in RPM In synchronous operation as specified speed in RPM for the slave drive unit
Bus connection	9-pin Plug Sub-D
Fieldbus coupling	CANopen Ethernet
Max. fieldbus transmission speed	1 Mbit/s
Mounting type	Tightened On sub-base
Materials note	Conforms to RoHS Contains PWIS substances