


hinge cylinder

DFAW-50- -

Part number: 2676213
Product to be discontinued

FESTO

Type to be discontinued. Available until 2019. See Support Portal for alternative products.



Data sheet

Overall data sheet – Individual values depend upon your configuration.

| Feature | Value |
|--|---|
| Stroke | 10 ... 200 mm |
| Piston diameter | 50 mm |
| Cushioning | PPS: Self-adjusting pneumatic end-position cushioning |
| Assembly position | Any |
| Design structure | Piston Piston rod with rod clevis Swivel mounting on bearing cap Cylinder barrel |
| Speed regulation | Integrated flow control valves on both sides |
| Position detection | For proximity sensor |
| Piston-rod end | Male thread with rod clevis |
| Operating pressure | 1 ... 10 bar |
| Mode of operation | double-acting |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 0 - No corrosion stress |
| Ambient temperature | -10 ... 60 °C |
| Cushioning length | 24 mm |
| Theoretical force at 6 bar, return stroke | 990 N |
| Theoretical force at 6 bar, advance stroke | 1,178 N |
| Additional weight per 10 mm stroke | 37 g |
| Additional mass factor per 10 mm of stroke | 25 g |
| alternative connections | See product drawing |
| Mounting type | With swivel mounting on bearing cap with accessories |
| Pneumatic connection | G1/4 |
| Material rod clevis | Aluminium die cast Anodised |
| Materials note | Conforms to RoHS |
| Material wiper seal | Bronze |
| Material cover | Aluminium die cast |
| Material seals | NBR |
| Material piston rod | Heat-treatment steel hard-chromium plated |
| Material cylinder barrel | Wrought Aluminium alloy Anodised |