


Axial kit EAMM-A-D100-120G-S1

Part number: 2946765

FESTO



Data sheet

Feature	Value
Mounting position	optional
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP65
Ambient temperature	-10 °C...60 °C
Transmittable torque	143 Nm
Product weight	3520 g
Interface code, actuator	D100B
Interface code, motor in	120G
Note on materials	RoHS-compliant