

Round cylinder DSNU-S-16-125-PPS-A-MQ

Part number: 5217245

FESTO



Data sheet

Feature	Value
Stroke	125 mm
Piston diameter	16 mm
Piston rod thread	M6
Cushioning	Self-adjusting pneumatic end-position cushioning
Mounting position	optional
Design	Piston Piston rod Cylinder barrel
Position detection	Via proximity switch
Operating pressure	0.08 MPa...1 MPa 0.8 bar...10 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	-20 °C...80 °C
Cushioning length	12 mm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	103.7 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	120.6 N
Moving mass for 0 mm stroke	18.3 g
Additional moving mass per 10 mm stroke	2 g
Basic weight for 0 mm stroke	48.9 g
Additional weight per 10 mm stroke	4.8 g
Type of mounting	With accessories
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover	Anodised wrought aluminium alloy
Material seals	TPE-U(PU)
Material piston rod	High-alloy stainless steel

Feature	Value
Material cylinder barrel	High-alloy stainless steel