

Controller CPX-E-CEC-C1

Part number: 5226780

FESTO



RD	0	1	RD
BU	2	3	BU

Data sheet

Feature	Value
Dimensions (W x L x H)	42.2 mm x 76.5 mm x 125.8 mm
Grid dimension	18.9 mm
Type of mounting	With H-rail
Max. number of modules	10
Product weight	145 g
Mounting position	Vertical Horizontal
Ambient temperature	-5 °C...50 °C
Note on ambient temperature	-5 - 60°C for vertical installation
Storage temperature	-20 °C...70 °C
Relative air humidity	95 % Non-condensing
Degree of protection	IP20
Corrosion resistance class CRC	0 - No corrosion stress
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27
Protection against direct and indirect contact	PELV
LABS (PWIS) conformity	VDMA24364 zone III
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
CE marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
KC mark	KC-EMV
Approval	RCM trademark c UL us listed (OL)
Certificate issuing authority	UL E239998
Note on materials	RoHS-compliant
Material housing	PA

Feature	Value
Diagnostics via LED	Force mode Module status Network status, engineering port 1 EtherCAT® network status Run Power supply, electronics/sensors Load power supply System fault
Operator controls	DIL switch for RUN/STOP
IP address setting	DHCP Via CODESYS
Fieldbus interface	Ethernet
Field bus, protocol	EtherCAT® EtherCAT CoE EtherCAT EoE EtherCAT FoE EtherCAT Master
Field bus, connection type	Socket
Field bus, connection system	RJ45
Field bus, connection pattern	8
Field bus interface, electrical isolation	yes
Field bus interface, transmission rate	100 Mbit/s
Ethernet interface, connection type	Socket
Ethernet interface, protocol	EasyIP Modbus® TCP OPC UA TCP/IP
Ethernet interface, function	Diagnostics
Ethernet interface, connection system	RJ45
Ethernet interface, number of pins/wires	8
Ethernet interface, transmission rate	10 Mbit/s 100 Mbit/s
Max. address volume, inputs	64 Byte
Max. address volume, outputs	64 Byte
System parameters	Diagnostic memory Fail-safe response System start
Module parameters	Channel alarms bundling Undervoltage diagnostics Channel alarms for undervoltage Process value representation of analogue modules
Configuration support	CODESYS V3
Additional functions	CODESYS V3
CPU data	128 MB RAM Dual Core 650 MHz
Power supply, function	Electronics and sensors
Power supply, connection type	Terminal strip
Power supply, note on connection type	> 4 A und UL 2x Klemmleiste zur Spannungsversorgung
power supply, connection system	Spring-loaded terminal
Power supply, number of pins/wires	4
Nominal DC operating voltage, electronics/sensors	24 V
Permissible voltage fluctuations for electronics/sensors	± 25%
Power supply, conductor diameter	0.2 mm²...1.5 mm²
Power supply, note on conductor diameter	0.2 - 2.5 mm² for flexible conductors without wire ferrule
Max. power supply	8 A
Intrinsic current consumption at nominal operating voltage for electronics/sensors	Typically 65 mA
Power failure bridging	20 ms
Reverse polarity protection	24 V sensor supply against 0 V sensor supply

Feature	Value
Programming software	CODESYS provided by Festo
Program memory	12 MB user program
Processing time	Approx. 200 µs/1 k instruction
Function modules	And others Read CPX-E module diagnostics CPX-E diagnostic status Copy CPX-E diagnostic trace
Buffering time real-time clock	3 Weeks
Flag	120 kB retentive data CODESYS variable concept