


Pressure gauge kit DPA-63-10-MA-SET

Part number: 526096

FESTO

for pressure booster



Data sheet

Feature	Value
Conforms to standard	EN 837-1
Nominal size of pressure gauge	40
Design structure	Bourdon-tube pressure gauge
Mounting type	with external (male) thread
Operating pressure	10 bar
Measurement accuracy class	2,5
Protection class	IP43
Ambient temperature	5 ... 60 °C
PWIS conformity	VDMA24364-B1/B2-L
Materials note	Conforms to RoHS
Assembly position	Any
Pneumatic connection	G1/8
Product weight	250 g