

angle seat valve

VZXF-L-M22C-M-B-N1-240-M1-V4B2T-50-10

Part number: 3539785

FESTO

Pneumatically actuated angle seat valve in stainless steel. Under seat version, safety position closed, NPT thread, nominal width 1".



Data sheet

| Feature | Value |
|---|--|
| Design structure | Poppet valve with piston actuator |
| Type of actuation | pneumatic |
| Sealing principle | soft |
| Assembly position | Any |
| Mounting type | Line installation |
| Line connection | Threaded coupling 1 NPT to ANSI/ASME B 1.20.1 |
| Nominal size | 24 mm |
| Valve function | 2/2 closed, monostable |
| Flow direction | non reversible |
| Pressure of medium | 0 ... 1 MPa |
| Medium pressure | 0 ... 10 bar |
| Nominal pressure of process valve | 40 |
| Exhaust-air function | not throttleable |
| Type of reset | mechanical spring |
| Type of piloting | With external control |
| Pneumatic connection | Female thread G1/8 |
| Operating pressure MPa | 0.6 ... 1 MPa |
| Operating pressure | 6 ... 10 bar 87 ... 145 psi |
| Medium | Vapour Mineral oil-based hydraulic oil Inert gases Mineral oil Water Filtered compressed air, degree of filtration 200 µm Neutral fluids |
| Flow direction | Below valve seat, for gaseous and liquid media |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Max. viscosity | 600 mm ² /s |
| Medium temperature | -40 ... 200 °C |
| Ambient temperature | -10 ... 60 °C |
| Flow rate Kv | 11 m ³ /h |
| Materials note | Conforms to RoHS |
| PWIS conformity | VDMA24364 zone III |
| Material process valve housing | Stainless steel casting |
| Material number, process valve housing | 1.4408 |
| Material spindle seal | PTFE |
| Material seat seal | PTFE |
| Product weight | 1,600 g |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| Material drive housing | Nickel-plated brass |