

vacuum generator VAD-MYB-1/8



Part number: 35553
Classic - do not use for new projects



With integrated solenoid valve

Unlubricated air is recommended.

Modern alternatives can be found by entering the first four characters of the type code in the search field.



Data sheet

Feature	Value
Nominal size, Laval nozzle	0.7 mm
Assembly position	Any
Ejector characteristic	High vacuum
Integrated function	Electrical on-off valve
Design structure	T-shaped
Operating pressure	1.5 ... 8 bar
Max. vacuum	85 %
Duty cycle	100 %
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Medium temperature	0 ... 40 °C
Protection class	IP65
Ambient temperature	0 ... 40 °C
Product weight	80 g
Electrical connection	Plug
Mounting type	with internal (female) thread
Pneumatic connection, port 1	M5
Vacuum connection	G1/8
Material housing	Aluminium