

Pressure regulator MS12-LR

Part number: 535021

FESTO



Data sheet

Feature	Value
Size	12
Series	MS
Actuator lock	Rotary knob with detent Rotary knob with integrated lock can be closed with accessories
Mounting position	optional
Design	Piloted diaphragm regulator
Controller function	Output pressure constant Via primary pressure compensation With secondary venting With return flow function
Pressure gauge (ANALOG) or Pressure display (DIGITAL)	With pressure gauge
Operating pressure	0.08 MPa...2.1 MPa 0.8 bar...21 bar
Pressure regulation range	0.15 bar...16 bar
Flow rate of secondary exhaust	600 l/min
Standard nominal flow rate	12000 l/min...22000 l/min
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
CE marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Type of mounting	Either: In-line installation Via mounting bracket
Material covering	PA
Note on materials	RoHS-compliant
Material underneath cover	Wrought aluminium alloy

Feature	Value
Material seals	NBR
Material spring	Spring steel
Material housing	Die-cast aluminium
Material membrane	NBR
Material valve stem	Wrought aluminium alloy NBR High-alloy stainless steel