

filter MS12-LF

Part number: 535023

FESTO

For manifold assembly, with G thread.



Exemplary representation

Data sheet

Overall data sheet – Individual values depend upon your configuration.

| Feature | Value |
|---------------------|---|
| Size | 12 |
| Series | MS |
| Assembly position | Vertical +/- 5° |
| Design structure | Sintered filter with centrifugal separator |
| Operating pressure | 0.8 ... 20 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [-:9:-] Compressed air to ISO 8573-1:2010 [7:9:-] Inert gases |
| PWIS conformity | VDMA24364-B1/B2-L |
| Storage temperature | -10 ... 60 °C |
| Medium temperature | -10 ... 60 °C |
| Ambient temperature | -10 ... 60 °C |
| Mounting type | Line installation with accessories Optional |
| Material housing | Aluminium die cast |
| Material bowl | Wrought Aluminium alloy |