



# Compact cylinder DPDM-Q-10-15-S-PA

Part number: 4833121

FESTO



## Data sheet

Feature	Value
Stroke	15 mm
Piston diameter	10 mm
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Mode of operation	Single-acting Pushing
Design	Piston Piston rod Profile barrel
Position detection	Via proximity switch
Variants	Piston rod at one end
Protection against torque/guide	Guide rod with yoke
Operating pressure	0.2 MPa...0.8 MPa 2 bar...8 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C...80 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi)	38 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	38 N
Moving mass for 0 mm stroke	13 g
Additional moving mass per 10 mm stroke	1.3 g
Basic weight for 0 mm stroke	37 g
Additional weight per 10 mm stroke	7.5 g
Type of mounting	Either: With through-hole Via female thread
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy

<b>Feature</b>	<b>Value</b>
Material seals	NBR TPE-U(PU)
Material housing	Anodised wrought aluminium alloy
Material piston rod	High-alloy stainless steel