

# Motor cable NEBM-SF1W31-EH-2.6-Q15N-LE28

Part number: 5213342

FESTO



## Data sheet

| Feature  | Value   |
|--|---|
| Conforms to standard                                 | DIN 47100   |
| Cable designation                                    | Without inscription label holder                                  |
| Frequency of connection                              | 30  |
| Product weight                                       | 770 g   |
| Electrical connection 1, function                    | Field device side   |
| Electrical connection 1, design                      | Angular   |
| Electrical connection 1, connection type             | Plugs   |
| Electrical connection 1, cable outlet                | Angled  |
| Electrical connection 1, note on cable outlet        | 90°   |
| Electrical connection 1, connector system            | Connection pattern F1   |
| Electrical connection 1, number of connections/cores | 31  |
| Electrical connection 1, used connections/cores      | 31  |
| Electrical connection 1, type of mounting            | Snap-in locking   |
| Electrical connection 2, function                    | Controller side   |
| Electrical connection 2, connection type             | Cable   |
| Electrical connection 2, connector system            | Open end  |
| Electrical connection 2, number of connections/cores | 28  |
| Electrical connection 2, used connections/cores      | 28  |
| Operational voltage range DC                         | 0 V...50 V  |
| Nominal operating voltage DC                         | 24 V  |
| Current rating at 40° C                              | 0.5 A   |
| Immunity to surge                                    | 0.25 kV   |
| Cable length   | 2.6 m   |
| Cable characteristic                                 | Suitable for energy chains  |
| Test conditions cable                                | Test conditions on request  |
| Bending radius, fixed cable                          | 49.5 mm   |
| Bending radius, moving cable                         | 74.25 mm  |
| Cable diameter                                       | 9.9 mm  |
| Cable diameter tolerance                             | ± 0.2 mm  |
| Cable structure                                      | 1 x (6 x 0.35 mm <sup>2</sup> ) + 2 x (4 x 0.15 mm <sup>2</sup> ) |
| Nominal cross section conductor                      | 0.15 mm <sup>2</sup><br>0.35 mm <sup>2</sup>                      |

| <b>Feature</b>                             | <b>Value</b>                         |
|--|--------------------------------------|
| Wire ends                                  | Wire end sleeve                      |
| Degree of protection                       | IP20                                 |
| Note on degree of protection               | In assembled state                   |
| Ambient temperature                        | -20 °C...75 °C                       |
| Ambient temperature with moving cable      | -5 °C...70 °C                        |
| Storage temperature                        | -25 °C...55 °C                       |
| CE mark (see declaration of conformity)    | In accordance with EU RoHS Directive |
| CE marking (see declaration of conformity) | To UK RoHS instructions              |
| LABS (PWIS) conformity                     | VDMA24364 zone III                   |
| Note on materials                          | RoHS-compliant                       |
| Pollution degree                           | 1                                    |
| Corrosion resistance class CRC             | 1 - Low corrosion stress             |
| Material cable sheath                      | TPE-U(PUR)                           |
| Cable sheath colour                        | Black                                |
| Material housing                           | PA                                   |
| Housing colour                             | Black                                |
| Material electrical contact                | Copper alloy, tin-plated             |