

LRBS-3/8-D-O-K4-MIDI

Pressure regulator manifold

| Feature | Data/description |
|---|--|
| Size | Midi |
| Series | D |
| Actuator lock | Rotary knob with integrated lock |
| Assembly position | Any |
| Design structure | directly-controlled diaphragm regulator with looped-through compressed air supply |
| Controller function | with initial pressure compensation with secondary exhaust Output pressure constant |
| Pressure gauge | G1/4" prepared |
| Pressure control range | 0,5 - 12 bar |
| Inlet pressure 1 | 1 - 16 bar |
| Max. pressure hysteresis | 0,2 bar |
| Standard nominal flow rate | 3.200 l/min |
| Operating medium | Filtered compressed air, 40 µm filtration |
| Medium temperature | -10 - 60 °C |
| Ambient temperature | -10 - 60 °C |
| Product weight | 4.834 g |
| Mounting type | with accessories |
| Pneumatic connection, port 1 | G3/8 |
| Pneumatic connection, port 2 | G3/8 |
| Materials information for sub-base | Zinc die-casting |
| Materials information for control panel | Aluminium |
| Materials information for seals | NBR |

LRBS-3/8-D-O-K4-MIDI**Pressure regulator manifold**

| Feature | Data/description |
|--------------------------------|------------------|
| Materials information, housing | Zinc die-casting |