


# Proximity sensor SIEF-M8NB-NS-S-L

Part number: 538309

FESTO



## Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Approval	RCM trademark c UL us listed (OL)
CE mark (see declaration of conformity)	To EU EMC Directive
Measuring principle	Inductive
Rated operating distance	4 mm
Assured operating distance	3.24 mm
Reduction factors	Aluminium = 1.0 Stainless steel St 18/8 = 1.0 Copper = 1.0 Brass = 1.0 Steel St 37 = 1.0
Ambient temperature	-30 °C...85 °C
Repetition accuracy	0.08 mm
Switching output	NPN
Switching element function	N/O contact
Hysteresis	0.12 mm...0.6 mm
Max. switching frequency DC	2000 Hz
Max. output current	150 mA
Voltage drop	1.8 V
Short circuit current rating	Pulsed
Operational voltage range DC	10 V...30 V
Residual ripple	10 %
No-load supply current	15 mA
Reverse polarity protection	For all electrical connections
Electrical connection	3-pin M8x1 Plugs
Size	M8
Type of mounting	Via lock nut
Tightening torque	10 Nm
Mounting type	Partially flush

<b>Feature</b>	<b>Value</b>
Product weight	19 g
Material housing	PA High-alloy stainless steel
Switching status indication	Yellow LED
Degree of protection	IP67
Immunity to magnetic fields	Magnetic direct and alternating field
Corrosion resistance class CRC	4 - Very high corrosion stress
Additional information for sensor selection	Reduction factor 1, resistant to magnetic fields
Electrical output	NPN
Selection of sensor design	Standard