


Connecting cable KMP6-25P-20-10

Part number: 530048

FESTO



Data sheet

Feature	Value
Conforms to standard	DIN 41652
Cable designation	Without inscription label holder
Frequency of connection	50
Product weight	1600 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	Angular
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connector system	Sub-D
Electrical connection 1, number of connections/cores	25
Electrical connection 1, used connections/cores	25
Electrical connection 1, type of mounting	2x screw 4-40 UNC
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Cable
Electrical connection 2, connector system	Open end
Electrical connection 2, number of connections/cores	25
Electrical connection 2, used connections/cores	25
Operational voltage range DC	0 V...30 V
Nominal operating voltage DC	24 V
Current rating at 40° C	2.8 A
Immunity to surge	1 kV
Cable length	10 m
Cable characteristic	Standard
Test conditions cable	Test conditions on request
Bending radius, fixed cable	103 mm
Bending radius, moving cable	103 mm
Cable diameter	10.3 mm
Cable diameter tolerance	± 0.25 mm
Cable structure	20 x 0.25 mm ² + 5 x 0.34 mm ²
Nominal cross section conductor	0.25 mm ² 0.34 mm ²
Wire ends	Cut off bluntly

Feature	Value
Degree of protection	IP40
Note on degree of protection	In assembled state
Ambient temperature	-25 °C...70 °C
Ambient temperature with moving cable	-5 °C...70 °C
Storage temperature	-25 °C...75 °C
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
CE marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Pollution degree	2
Material cable sheath	PVC
Cable sheath colour	grey
Material housing	PBT-reinforced
Housing colour	grey
Material screw-type lock	Nickel-plated brass
Material electrical contact	Gold-plated copper alloy