


Linear gantry DHSL-DGE25SP-HMPL16

Part number: 542981

FESTO

comprising electric spindle axis and light handling axis, precise positioning and a variety of modules. Defined interfaces to Festo's rotary and gripper range. Order as a mounting kit or completely assembled and installed.

Please click above on symbol FAX request, to obtain a non-binding offer to fulfil your requirements.



Data sheet

Feature	Value
Assembly	Linear gantry 1.0
Effective load	0 ... 2 kg
Drive unit, Z axis	HMPL-16
Drive system, Z axis	Pneumatic
Intermediate position, Z axis	x1
Stroke, Z axis	0 ... 160 mm
Repetition accuracy in the end position, Z axis	± 0,02 mm
Repetition accuracy in the intermediate position, Z axis	± 0,02 mm
Drive unit, Y axis	DGE-25-SP
Drive system, Y axis	Electrical With spindle
Intermediate position, Y axis	Any
Stroke, Y axis	0 ... 1,000 mm
Repetition accuracy in the end position, Y axis	± 0,02 mm
Repetition accuracy in the intermediate position, Y axis	± 0,02 mm