


Planar surface gantry DHSF-DGE25RF-DGE25RF

Part number: 543020

FESTO

comprising electric toothed belt axes with roller guides and passive guide axis, exact and very dynamic positioning. Defined interfaces to Festo's rotary and gripper range. Order as a mounting kit or completely assembled and installed.

Please click above on symbol FAX request, to obtain a non-binding offer to fulfil your requirements.



Data sheet

| Feature | Value |
|--|--|
| Assembly | Planar surface gantry 1.0-3.0 |
| Effective load | 0 ... 3 kg |
| Drive unit, Y axis | DGE-25-ZR-RF |
| Drive system, Y axis | Electrical Toothed belt with roller guide |
| Intermediate position, Y axis | Any |
| Stroke, Y axis | 0 ... 1,300 mm |
| Repetition accuracy in the end position, Y axis | ± 0,1 mm |
| Repetition accuracy in the intermediate position, Y axis | ± 0,1 mm |
| Drive unit, X axis | DGE-25-ZR-RF |
| Drive system, X axis | Electrical Toothed belt with roller guide |
| Intermediate position, X axis | Any |
| Stroke, X axis | 0 ... 2,000 mm |
| Repetition accuracy in the end position, X axis | ± 0,1 mm |
| Repetition accuracy in the intermediate position, X axis | ± 0,1 mm |