


axial kit EAMM-A-D40-42C

Part number: 543156

FESTO

Suitable for electric drives.



Data sheet

Feature	Value
Assembly position	Any
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	12.5 Nm
Product weight	370 g
Interface code, actuator	D40A D40C
Interface code, motor in	42C
Materials note	Contains PWIS substances Conforms to RoHS