

# electrical interface

## CPV14-GE-DN3-8

Part number: 546200  
Product to be discontinued

FESTO



## Data sheet

Feature	Value
CP string extension	Yes 32 inputs 32 outputs
Fieldbus interface	Optional - 5-pin screw terminal strip - Socket and plug, M12x1, 5-pin, A coded - Sub-D, 9-pin, socket
Device-specific diagnostics	ConditionMonitoring Missing module in CP string Short-circuit / overload, outputs Short-circuit / overload, inputs Undervoltage, valve terminal (extension) Undervoltage, output module Undervoltage, sensor supply power Undervoltage, valve terminal
Communication types	Change of State Polling Strobbed I/O
Configuration support	EDS file and graphic symbol
Maximum number of solenoid coils with string extension	48
Max. number of solenoid coils	16
Polarity protected	for all electrical connections
Additional functions	Condition Counter
Baud rate	125, 250, 500 kBit/s Adjustment via switch module
Operating voltage range DC	20.4 ... 26.4 V
Maximum number of outputs	16 solenoid coils and 32 outputs 48 valve coils
Maximum number of inputs	32
Nominal operating voltage DC	24 V
Power failure buffering	10 ms
Residual ripple	4 V <sub>ss</sub>
Current consumption at nominal operating voltage, load	Depending on valve type
Current consumption at nominal operating voltage	Electronics: ≤ 200 mA Sensor supply power: depends upon sensor
Corrosion resistance classification CRC	1 - Low corrosion stress
Storage temperature	-20 ... 70 °C
Protection class	IP20 IP65
Ambient temperature	-5 ... 50 °C
Authorisation	c UL us - Recognized (OL)
Addressing range	0 ... 63 Adjustment via switch module
Fieldbus certification	ODVA
Electrical isolation, fieldbus interface	Optocoupler
Bus-specific LED display	MNS: DeviceNet Status

Feature	Value
Product-specific LED display	12/14: switching status at valves PS: operating voltage for electronics and load supply
Product ID	product type: pneumatic valve (27 dec.) Product code: 8942 dec.
Material cover	PA-reinforced
Material seals	CR NBR
Material housing	Aluminium die cast
Materials note	Conforms to RoHS