

Fine filter MS12-LFM-G-BUV

Part number: 537153

FESTO



Data sheet

Feature	Value
Series	MS
Size	12
Design	Fibre filter
Grade of filtration	1 µm
Condensate drain	Fully automatic Manual, non-detenting
Operating pressure	2 bar...12 bar
Operating medium	Compressed air to ISO 8573-1:2010 [6:8:4] Inert gases
Air purity class at output	Compressed air to ISO 8573-1:2010 [5:7:3]
Filter efficiency	99.99 %
Max. condensate volume	400 cm ³
Bowl guard	Integrated as metal bowl
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	5 °C...60 °C
Ambient temperature	5 °C...60 °C
Storage temperature	-10 °C...60 °C
Type of mounting	Either: In-line installation Via mounting bracket
Mounting position	Vertical +/-5°
Material housing	Die-cast aluminium
Material covering	PA
Material filter	Borosilicate fibre
Material bowl	Wrought aluminium alloy
Material screen	PC
Material seals	NBR
Note on materials	RoHS-compliant
Product weight	7000 g