



Diffuse sensor SOEG-RT-M18-PA-S-2L

Part number: 547913

FESTO



Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Approval	RCM trademark c UL us listed (OL)
CE mark (see declaration of conformity)	To EU EMC Directive
Measured variable	Position
Measuring principle	Optoelectronic
Measurement method	Diffuse sensor
Type of light	Red
Operating distance	40 mm...600 mm
Ambient temperature	-25 °C...55 °C
Switching output	PNP
Switching element function	Antivalent
Hysteresis	60 mm
Max. switching frequency	1000 Hz
Max. output current	200 mA
Voltage drop	2 V
Short circuit current rating	Pulsed
Operational voltage range DC	10 V...36 V
Residual ripple	20%
No-load supply current	20 mA
Reverse polarity protection	For all electrical connections
Electrical connection	4-pin M12x1 Plugs
Size	M18
Type of mounting	Via lock nut
Tightening torque	20 Nm
Mounting position	optional
Product weight	53 g
Material housing	Brass Chrome-plated

Feature	Value
Switching status indication	Yellow LED
Function reserve indication	Green LED
Setting options	Potentiometer
Setting range lower limit	40 mm
Setting range upper limit	600 mm
Ambient temperature with moving cable	-5 °C...55 °C
Degree of protection	IP65 IP67
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III