



retro-reflective sensor SOEG-RSP-M18W-PS-S-2L

Part number: 537700
Product to be discontinued

FESTO

With polarised light, round design, with 90° angled beam
Type to be discontinued. Available until 2024. See Support Portal for alternative products.



Data sheet

| Feature | Value |
|--|-----------------------------------|
| Design | Round |
| Conforms to standard | EN 60947-5-2 |
| Authorisation | RCM Mark c UL us - Listed (OL) |
| CE mark (see declaration of conformity) | to EU directive for EMC |
| Measured variable | Position |
| Measuring principle | Optoelectronic |
| Measurement method | Retro-reflective sensor |
| Type of light | Red, polarised |
| Working range | 2,000 mm |
| Ambient temperature | -25 ... 55 °C |
| Switch output | PNP |
| Switching element function | Dark switching |
| Max. switching frequency | 1,000 Hz |
| Max. output current | 200 mA |
| Voltage drop | ≤ 2 V |
| Short circuit strength | Pulsing |
| Operating voltage range DC | 10 ... 36 V |
| Residual ripple | 20 % |
| Idle current | 15 mA |
| Polarity protected | for all electrical connections |
| Electrical connection | 3-pin M12x1 Plug |
| Size | M18x1 |
| Mounting type | with lock nut |
| Tightening torque | 20 Nm |
| Product weight | 56 g |
| Material housing | Brass Chromed-plated |
| Material of union nut | Brass Chromed-plated |
| Operating status display | Yellow LED |
| Operating reserve display | Green LED |
| Ambient temperature with flexible cable installation | -5 ... 55 °C |
| Protection class | IP65 IP67 |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-B2-L |