

Round cylinder DSNU-5/8^{'''} - -PPV-A-S2

Part number: 548521

FESTO



Data sheet

Feature	Value
Stroke	0,4 in...8 in
Piston diameter	5/8"
Piston rod thread	10-32 UNF-2A
Based on standard	ISO 6432
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	optional
Piston-rod end	Male thread
Design	Piston Piston rod
Position detection	Via proximity switch
Variants	Through piston rod
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-4 °F...176 °F
Impact energy in end positions	0,111 ft-lbf
Cushioning length	0,47 in
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	20,7 lbf
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	24,1 lbf
Moving mass for 0 mm stroke	652 oz
Additional weight per 10 mm stroke	57,1 oz
Type of mounting	With accessories
Pneumatic connection	10-32 UNF-2B
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	NBR TPE-U(PU)

Feature	Value
Material piston rod	High-alloy stainless steel
Material cylinder barrel	High-alloy stainless steel