


Multi-pin CPV14-VI-P2-1/8-C

Part number: 539498

FESTO



Data sheet

| Feature | Value |
|---|---|
| CE mark (see declaration of conformity) | To EU Explosion Protection Directive (ATEX) |
| CE marking (see declaration of conformity) | To UK EX instructions To UK RoHS instructions |
| Explosion protection certification outside the EU | EPL Db (GB) EPL Db (IEC-EX) EPL Dc (IECEX) EPL Gb (GB) EPL Gb (IECEX) EPL Gc (IECEX) |
| Explosion protection | Zone 1 (ATEX) Zone 1 (IEC-EX) Zone 1 (UKEX) Zone 2 (ATEX) Zone 2 (IEC-EX) Zone 21 (ATEX) Zone 21 (IEC-EX) Zone 21 (UKEX) Zone 22 (ATEX) Zone 22 (IEC-EX) |
| Certificate issuing authority | IECEx TUR 12.0002X TÜV 06 ATEX 7334 X German Technical Control Board (TÜV) 21 UKEX 7013 X |
| ATEX category gas | II 2G |
| ATEX category dust | II 2D |
| Explosion ignition protection type for gas | Ex eb IIC Gb |
| Explosion ignition protection type for dust | Ex tb IIIC Db |
| Explosion ambient temperature | -10°C ≤ Ta ≤ +60°C |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Product weight | 500 g |
| Note on materials | RoHS-compliant |
| Material seals | NBR |
| Material plate | Wrought aluminium alloy |