


Proximity sensor SIES-8M-PO-24V-K-7,5-OE

Part number: 551391

FESTO



Data sheet

Feature	Value
Design	For T-slot
Conforms to standard	EN 60947-5-2
Approval	RCM trademark c UL us listed (OL)
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
KC mark	KC-EMV
Note on materials	RoHS-compliant
Measured variable	Position
Measuring principle	Inductive
Rated operating distance	1.5 mm
Reduction factors	Aluminium = 0.62 Stainless steel V2A = 0.95 Copper = 0.6 Brass = 0.72 Steel St 37 = 1.0
Ambient temperature	-25 °C...70 °C
Repetition accuracy with constant conditions	≤ 0.05 mm, approach from the side
Switching output	PNP
Switching element function	N/C contact
Switch-on time	0,1 µs
Max. switching frequency	4500 Hz
Max. output current	150 mA
Max. switching capacity DC	4.5 W
Voltage drop	2 V
Inductive protective circuit	Integrated
Min. load current	0 mA
Off-state current	1E-11 µA
Short circuit current rating	Pulsed
Overload protection	Available
Operational voltage range DC	10 V...30 V
Residual ripple	10 %
No-load supply current	10 mA

Feature	Value
Reverse polarity protection	For all electrical connections
Electrical connection 1, connection type	Cable
Electrical connection 1, connector system	Open end
Electrical connection 1, number of connections/cores	3
Connection outlet orientation	In-line
Test conditions cable	Bending strength: to Festo standard Test conditions on request Energy chain: > 5 million cycles, bending radius 75 mm
Cable length	7.5 m
Cable characteristic	Standard/suitable for energy chains
Cable sheath colour	grey
Material cable sheath	TPE-U(PU)
Material insulating sheath	PP
Size	Slot 8
Type of mounting	Flush with T-slot Screw-clamped Insertable in the slot from above
Tightening torque	0.6 Nm
Mounting position	optional
Mounting type	Flush
Housing colour	Black
Material housing	PA PUR High-alloy stainless steel
Switching status indication	Yellow LED
Ambient temperature with moving cable	-5 °C...70 °C
Degree of protection	IP65 IP67
Insulation voltage	50 V
Immunity to surge	0.8 kV
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 4 according to ISO 14644-1
Pollution degree	3
Additional information for sensor selection	For T-slot
Electrical output	PNP
Selection of sensor design	Special design