



# solenoid valve

## NVF3-5/2K-1/4-120-EX

Part number: 541647

FESTO



## Data sheet

Feature	Value
Valve function	5/2 closed, monostable
Type of actuation	electrical
Width	76 mm
Standard nominal flow rate	900 l/min
Operating pressure	2 ... 10 bar
Design structure	Poppet seat
Type of reset	mechanical spring
Nominal size	7 mm
Exhaust-air function	throttleable
Sealing principle	soft
Assembly position	Any
Conforms to standard	VDI/VDE 3845 (NAMUR)
Manual override	detenting Pushing
Type of piloting	Piloted
Flow direction	non reversible
Freedom from overlap	No
b value	0.33
C value	4.2 l/sbar
Switching time off	100 ms
Switching time on	50 ms
Characteristic coil data	120 V AC: 60 Hz, pick-up power 11.5 VA, holding power 6.5 VA
Explosion protection certification outside the EU	Class I, Div. 1 (US) Class I, Div. 2 (US) Class II, Div. 1 (US) Class II, Div. 2 (US) Class III, Div. 1 (US) Class III, Div. 2 (US) EPL Gb (US) EPL Gc (US)
Certificate issuing department	FM 3026030
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1
Medium temperature	-5 ... 40 °C
Ambient temperature	-5 ... 40 °C
Product weight	500 g
Mounting type	On sub-base
Scavenging orifice connection	Internal
Pilot exhaust port 84	M5
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	NAMUR port pattern
Pneumatic connection, port 3	G1/4
Pneumatic connection, port 4	NAMUR port pattern
Pneumatic connection, port 5	G1/4
Materials information for seals	NBR TPE-U(PU)
Materials information, housing	Aluminium die cast Anodised