

Micro filter MS9-LFM-N3/4-AUM-DA

Part number: 553094

FESTO



Data sheet

Feature	Value
Series	MS
Size	9
Design	Fibre filter
Grade of filtration	0.01 µm
Condensate drain	Manually rotating
Operating pressure	0 bar...20 bar
Operating medium	Compressed air to ISO 8573-1:2010 [6:8:4]
Air purity class at output	Compressed air to ISO 8573-1:2010 [1:7:2]
Max. standard flow rate for clean air class	6500 l/min
Min. standard flow rate for clean air class	325 l/min
Filter efficiency	99.9999 %
Max. condensate volume	225 ml
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Storage temperature	-10 °C...60 °C
Residual oil content	0.01 mg/m ³
Differential pressure display	Visual display
Type of mounting	Either: In-line installation With accessories
Mounting position	Vertical +/-5°
Pneumatic connection, port 1	3/4 NPT
Pneumatic connection, port 2	3/4 NPT
Material housing	Die-cast aluminium
Material covering	PA
Material filter	Borosilicate fibre
Material bowl	Wrought aluminium alloy
Material screen	PA

Feature	Value
Material seals	NBR
Product weight	2000 g