


connecting cable MHJ9-KMH-0,5-MF

Part number: 553121

FESTO



Data sheet

Feature	Value
Authorisation	RCM Mark
Additional functions	Spark arresting Reduction of holding current with energy recovery Safety shut-off
Mounting type	with through hole with top-hat rail Optional
Assembly position	Any
Product weight	40 g
Electrical connection	2-pin / 2-pin / 4-wire Straight socket / straight socket / cable
Operating voltage range DC	12 ... 53 V
Polarity protected	for operating voltage
Note on operation	Power supply unit must be able to supply at least 1.7 A without voltage drop
Information on power consumption	Low-current phase 2.0 W, high-current phase 7.0 W, per channel
Duty cycle	100 % Observe notes on operating the solenoid valves
Trigger signal range DC	3 ... 30 V
Note on feeder current	Linear rise 0.09 - 0.44 mA with a trigger signal of 3 - 15 V 0.44-15.44 mA with a trigger signal of 15-30 V
Input resistance	34 kOhm
Cable length	0.5 m
Cable attribute	For static applications
Protection class	IP40
Ambient temperature	-5 ... 50 °C
CE mark (see declaration of conformity)	to EU directive for EMC in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materials note	Conforms to RoHS
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Material cable sheath	PVC
Material housing	POM