

# Linear gantry


## DHSL-2DGE40SP-HMP25

Part number: 543011

FESTO

comprising an electric spindle axis with passive guide axis and modular handling axis, precise positioning and robust. Defined interfaces to Festo's rotary and gripper range. Order as a mounting kit or completely assembled and installed.

Please click above on symbol FAX request, to obtain a non-binding offer to fulfil your requirements.



### Data sheet

Feature	Value
Assembly	Linear gantry 4.0
Effective load	0 ... 10 kg
Drive unit, Z axis	HMP-25
Drive system, Z axis	Pneumatic
Intermediate position, Z axis	x1
Stroke, Z axis	0 ... 400 mm
Repetition accuracy in the end position, Z axis	± 0,02 mm
Repetition accuracy in the intermediate position, Z axis	± 0,02 mm
Drive unit, Y axis	2x DGE-40-SP
Drive system, Y axis	Electrical With spindle
Intermediate position, Y axis	Any
Stroke, Y axis	0 ... 1,000 mm
Repetition accuracy in the end position, Y axis	± 0,02 mm
Repetition accuracy in the intermediate position, Y axis	± 0,1 mm